Rittal – The System.

Faster – better – everywhere.



KX 1585.000

KX Bus Housings

State: 11/6/2026 (Source: www.rittal.com/us-en)

KX 1585.000 - KX Bus Housings Stainless steel

The stainless steel KX bus housing offers easy access with the standard 180° hinges and has a high protection rating of IP66.





Features

Model No.	KX 1585.000
Product description	The small enclosure KX, bus enclosure KX, stainless steel allows for a flexible interior installation and provides easy access with the standard 180° hinges.
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal Hinge: Die-cast zinc
Surface finish	Housing and cover: Brushed, grain 180 180° hinges: Chrome-plated
Supply includes	Housing with cover 180° hinges Quick-release fasteners including plastic bushings
Dimensions	Width: 400 mm Height: 200 mm Depth: 120 mm Width: 15.7 ″ Height: 7.87 ″ Depth: 4.72 ″
Protection category IP to EN 60 529	IP 66

© Rittal 2026

Features

Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 4X NEMA 12
Type rating according to 508A	Type 1 Type 3R Type 4 Type 4X Type 12
Material thickness - cover	1.25 mm 0.05 ″
Material thickness - enclosure	1.25 mm 0.05 ″
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	3.2 kg
Gross weight	3.46 kg
PCF/VE (cradle-to-gate)	13.75
Customs tariff number	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	KX Bus housing, WHD: 400x200x120 mm, stainless steel 1.4301, with hinged cover, with quick-release fasteners

Approvals

Approvals

Approvals	Bureau Veritas C-UL DNV Lloyds Register
Explanations	Declaration of conformity PCF-declaration