Rittal – The System.

Faster – better – everywhere.





KX 1610.000

KX bus housing, carbon steel, with mini cam lock

State: 12/14/2025 (Source: rittal.com/us-en)



KX 1610.000 - KX bus housing, carbon steel, with mini cam lock

Wall-mounted enclosure made of carbon steel, with cover and viewing window. Protection category IP 65/NEMA 12. For installation of most brands of bus modules and sensors.







Features

Model No.	KX 1610.000
Version	with viewing window
Material	Housing: Carbon steel Cover: Carbon steel, all-round foamed-in PU seal Viewing window: Polycarbonate, 4 mm1
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with hinged cover Sight glass in cover Mini-fasteners
Protection category NEMA	NEMA 1 NEMA 12
Protection category IP to EN 60 529	IP 65
Type rating according to UL 50E	Type 1 Type 12

© Rittal 2025 2

Features

IK code	IK08
Dimensions	Width: 400 mm Height: 200 mm Depth: 155 mm Width: 15.7 " Height: 7.87 " Depth: 6.1 "
Material thickness - cover	1.25 mm 0.05 ″
Material thickness - enclosure	1.25 mm 0.05 ″
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	3.9
Gross weight	3.95
PCF/VE (cradle-to-gate)	19.8 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	84879059
EAN	4028177816671
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas
	C-UL
	DNV-GL
	Lloyds Register of Shipping

© Rittal 2025 3

Approvals

Explanations

Manufacturer's declaration
Declaration of conformity
Declaration of conformity UK

PCF-declaration

© Rittal 2025 4