Rittal - The System.

Faster – better – everywhere.





KX 1611.100

Bus housing KX, carbon steel, with double-bit insert

State: 10/31/2025 (Source: rittal.com/us-en)



KX 1611.100 - Bus housing KX, carbon steel, with doublebit insert

Wall-mounted enclosure made of carbon steel, with cover and viewing window. Protection category IP 65/NEMA 12. For installation of most brands of bus modules and sensors.







Features

Model No.	KX 1611.100
Version	with viewing window
Material	Housing: Carbon steel
	Cover: Carbon steel, all-round foamed-in PU seal
	Viewing window: Polycarbonate, 4 mm1
	Mounting plate: Carbon steel, zinc-plated
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside,
	textured paint
Color	RAL 7035
Supply includes	Housing with hinged cover
	Sight glass in cover
	Mounting panel
	Cam lock with 3 mm double-bit insert
Protection category NEMA	NEMA 1
	NEMA 12
Protection category IP to EN 60 529	IP 65

© Rittal 2025 2

Features

Type rating according to UL 50E	Type 1
	Type 12
IK code	IK08
Dimensions	Width: 400 mm
	Height: 300 mm
	Depth: 155 mm
	Width: 15.7 "
	Height: 11.8 ″
	Depth: 6.1 "
Material thickness - cover	1.25 mm
	0.05 ″
Material thickness - enclosure	1.25 mm
	0.05 ″
Material thickness - mounting	2 mm
plate	0.08 ″
Base material	Carbon steel
Customs tariff number	84879059
EAN	4028177970083
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	C-UL	

© Rittal 2025 3