Rittal – The System.

Faster – better – everywhere.



KX 1528.000

KX terminal box, carbon steel, without flange

State: 11/15/2026 (Source: www.rittal.com/us-en)

KX 1528.000 - KX terminal box, carbon steel, without flange

The small enclosure KX, terminal box KX, without a gland plate allows for flexible interior installation while maintaining a high protection category.







Features

Model No.	KX 1528.000
Product description	The small enclosure KX, terminal box KX, without a gland plate allows for flexible interior installation while maintaining a high protection category.
Material	Housing: Carbon steel Cover: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with cover Mini cam lock
Dimensions	Width: 200 mm Height: 150 mm Depth: 80 mm Width: 7.87 ″ Height: 5.91 ″ Depth: 3.15 ″

© Rittal 2026

Features

Protection category IP to EN 60 529	IP 66
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Type rating according to 508A	Type 1 Type 3R Type 4 Type 12
IK code	IK08
Material thickness - cover	1.25 mm 0.05 ″
Material thickness - enclosure	1.25 mm 0.05 ″
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	1.35 kg
Gross weight	1.425 kg
PCF/VE (cradle-to-gate)	24.85 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	KX Terminal box, WHD: 200x150x80 mm, sheet steel, without mounting plate, with cover, without gland plate

Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
Certificates	Protection category
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK PCF-declaration