Rittal - The System.

Faster – better – everywhere.





AX 2260.930 AX wall-mounted housing, 3-part


State: 12/7/2025 (Source: rittal.com/us-en)



AX 2260.930 - AX wall-mounted housing, 3-part

The delivery concept of the three-part AX wall-mounted enclosure reduces complexity and increases flexibility. Thanks to the AX/VX modular system, the enclosures are suitable for various applications. The three-part structure ensures easy access.







Features

Model No.	AX 2260.930
Version	Wall-mounted housing IT
Material	Wall and hinged part: Carbon steel, 1.5 mm
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	Wall and hinged part: RAL 7035
	Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section: Flange (gland) plate, solid, top and bottom
	Hinged part with 25 mm pitch pattern in the front and rear frame
	two 19" profile angles at the front, fixed in place
	Designer viewing door
	Center part lock: 3 mm double bit
	Lock design – glazed door: Security lock 3524 E
	Mini-comfort handle
Height units	9 U

© Rittal 2025 2

Features

Dimensions	Width: 600 mm Height: 478 mm Depth: 373 mm Width: 23.6 " Height: 18.8 " Depth: 14.7 "
Installation depth	320 mm 12.6 ″
Clearances	Clearance width: 502 mm Clearance height: 417 mm Clearance width: 19.8 " Clearance height: 16.4 "
Depth hinged part	216 mm 8.5 ″
Depth of wall section	135 mm 5.31 ″
No. of locks	1
Load capacity of hinged part (static)	450 N
Load capacity wall section (static)	150 N
Base material	Carbon steel
Lock	Lock version: Mini-comfort handle Lock Insert: Security lock insert no. 3524 E
Protection category IP to EN 60 529	IP 54 in conjunction with solid gland plate top and bottom
Packaging unit	1 pc(s).
Net weight	26
Gross weight	26.333
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177983144

© Rittal 2025 3

Features

ETIM 9	EC002500	
ETIM 8	EC002500	
ECLASS 8.0	27180101	

Approvals

Explanations Declaration of conformity

© Rittal 2025