

Rittal – The System.

Faster – better – everywhere.



KX 1535.000

KX terminal box, carbon steel with flange

State: 5/21/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1535.000 - KX terminal box, carbon steel with flange

The small enclosure KX, terminal box KX, with a gland plate allows for flexible interior installation and simple cable entry with optimum use of space.



Features

Model No.	KX 1535.000
Material	Housing: Carbon steel Cover: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with cover Mini-fasteners Carbon steel flange plates with seals and assembly components
Protection category NEMA	NEMA 1 NEMA 12
Protection category IP to EN 60529	IP 55
Type rating according to UL 50E	Type 1 Type 12
IK code	IK08

Features

Dimensions	Width: 300 mm Height: 300 mm Depth: 120 mm Width: 11.8 ″ Height: 11.8 ″ Depth: 4.72 ″
Material thickness - cover	1.25 mm 0.05 ″
Material thickness - enclosure	1.25 mm 0.05 ″
Flange Plates	: 1 + 1 : 1 + 1
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	3.943 kg
Gross weight	4.24 kg
PCF/VE (cradle-to-gate)	34.37 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	KX Terminal box, WHD: 300x300x120 mm, sheet steel, without mounting plate, with cover, with gland plate

Approvals

Approvals

Approvals

Bureau Veritas
DNV
Lloyds Register
UL + C-UL (listed)

Certificates

Protection category

Explanations

Declaration of conformity
Declaration of conformity UK
PCF-declaration