Rittal - The System.

Faster – better – everywhere.





AX 2261.550 AX wall-mounted housing, 3-part


State: 11/5/2025 (Source: rittal.com/us-en)



AX 2261.550 - AX wall-mounted housing, 3-part

The delivery concept of the three-part AX wall-mounted enclosure reduces complexity and increases flexibility. Thanks to the AX/VX modular system, the enclosures are suitable for various applications. The three-part structure ensures easy access.







Features

Model No.	AX 2261.550
	7// 2201.000
Version	Wall-mounted housing IT
Material	Wall and hinged part: Carbon steel, 1.5 mm
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	Wall and hinged part: RAL 7035
	Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section: Flange (gland) plate, solid, top and bottom
	Hinged part with 25 mm pitch pattern in the front and rear frame,
	two 19" profile angles at the front, fixed in place
	Designer viewing door
	Center part lock: 3 mm double bit
	Lock design – glazed door: Security lock 3524 E
	Mini-comfort handle
Height units	15 U

© Rittal 2025 2

Features

class the basis of the product weight and self-declared Customs tariff number 94032080		
Clearances Clearance width: 502 mm Clearance height: 684 mm Clearance height: 26.9 " Depth hinged part 416 mm 16.4 " Depth of wall section 135 mm 5.31 " No. of locks 1 Load capacity of hinged part (static) Load capacity wall section (static) Carbon steel Lock Lock version: Mini-comfort handle Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 529 Packaging unit 1 pc(s). Net weight 40 Gross weight 41 Information regarding the PCF class the basis of the product weight and self-declared Customs tariff number 94032080	Dimensions	Height: 746 mm Depth: 573 mm Width: 23.6 " Height: 29.4 "
Clearance height: 684 mm Clearance width: 19.8 " Clearance height: 26.9 " Depth hinged part 416 mm 16.4 " Depth of wall section 135 mm 5.31 " No. of locks 1 Load capacity of hinged part (static) Load capacity wall section (static) 250 N Base material Carbon steel Lock Lock Lock version: Mini-comfort handle Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 529 Packaging unit 1 pc(s). Net weight 40 Gross weight Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	Installation depth	
Depth of wall section 135 mm 5.31 ″ No. of locks 1 Load capacity of hinged part (static) Load capacity wall section (static) 250 N Base material Carbon steel Lock Lock version: Mini-comfort handle Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 1P 54 in conjunction with solid gland plate top and bottom 529 Packaging unit 1 pc(s). Net weight 40 Gross weight 41 Information regarding the PCF class the basis of the product weight and self-declared Customs tariff number 94032080	Clearances	Clearance height: 684 mm Clearance width: 19.8 ″
No. of locks 1 Load capacity of hinged part (static) Load capacity wall section (static) 250 N Base material Carbon steel Lock Lock version: Mini-comfort handle Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 1P 54 in conjunction with solid gland plate top and bottom 529 Packaging unit 1 pc(s). Net weight 40 Gross weight 41 Information regarding the PCF category B: PCF value (cradle-to-gate) calculated approximately of class the basis of the product weight and self-declared Customs tariff number 94032080	Depth hinged part	
Load capacity of hinged part (static) Load capacity wall section (static) Base material Lock Lock version: Mini-comfort handle Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 IP 54 in conjunction with solid gland plate top and bottom 529 Packaging unit 1 pc(s). Net weight 40 Gross weight 41 Information regarding the PCF category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	Depth of wall section	
(static) Load capacity wall section (static) 250 N Base material Carbon steel Lock Lock version: Mini-comfort handle Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 IP 54 in conjunction with solid gland plate top and bottom 529 Packaging unit 1 pc(s). Net weight 40 Gross weight 41 Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	No. of locks	1
Base material Carbon steel Lock Lock version: Mini-comfort handle Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 IP 54 in conjunction with solid gland plate top and bottom Packaging unit 1 pc(s). Net weight 40 Gross weight 41 Information regarding the PCF class Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080		750 N
Lock Lock Version: Mini-comfort handle Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 IP 54 in conjunction with solid gland plate top and bottom Packaging unit 1 pc(s). Net weight 40 Gross weight 41 Information regarding the PCF class the basis of the product weight and self-declared Customs tariff number 94032080	Load capacity wall section (static)	250 N
Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 529 Packaging unit 1 pc(s). Net weight 40 Gross weight Information regarding the PCF class the basis of the product weight and self-declared Customs tariff number Lock Insert: Security lock insert no. 3524 E IP 54 in conjunction with solid gland plate top and bottom 40 Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared	Base material	Carbon steel
Packaging unit 1 pc(s). Net weight 40 Gross weight 41 Information regarding the PCF category B: PCF value (cradle-to-gate) calculated approximately contains the basis of the product weight and self-declared Customs tariff number 94032080	Lock	
Net weight 40 Gross weight 41 Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately contains the basis of the product weight and self-declared 94032080	= *	IP 54 in conjunction with solid gland plate top and bottom
Gross weight Information regarding the PCF class Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	Packaging unit	1 pc(s).
Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately contained the basis of the product weight and self-declared Customs tariff number 94032080	Net weight	40
class the basis of the product weight and self-declared Customs tariff number 94032080	Gross weight	41
		Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
51N	Customs tariff number	94032080
EAN 40281//983342	EAN	4028177983342

© Rittal 2025 3

Features

ETIM 9	EC002500	
ETIM 8	EC002500	
ECLASS 8.0	27180101	

Approvals

Explanations Declaration of conformity

© Rittal 2025