

Rittal – The System.

Faster – better – everywhere.



undefined 2262.165

AX wall-mounted housing, 3-part

State: 6/16/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



undefined 2262.165 - AX wall-mounted housing, 3-part

With Blue e+ outlet filter

The delivery concept behind the three-part AX wall-mounted enclosures reduces complexity and enhances flexibility. The AX/VX modular system makes these enclosures suitable for a range of applications. The three-part structure ensures easy access.

Features

Model No.	2262.165
Version	Wall-mounted housing IT
Material	Wall and hinged part: Carbon steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	Wall and hinged part: RAL 7035 Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section: Flange (gland) plate, solid, top and bottom Hinged part with 25 mm pitch pattern in the front and rear frame, two 19" profile angles at the front, fixed in place Designer viewing door Lock design – glazed door: Security lock 3524 E Center part lock: 3 mm double bit Incl. grounding and assembly components 2 Blue e+ outlet filters (supplied loose) Comfort handle for lock inserts and 2-point locking
Height units	21 U
Dimensions	Width: 600 mm Height: 1,012 mm Depth: 673 mm Width: 23.6 " Height: 39.8 " Depth: 26.5 "
No. of locks	1
IK code	IK08

Features

Load capacity of hinged part (static)	750 N
Load capacity of wall section (static)	250 N
Base material	Carbon steel
Lock	Lock version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E
Protection category IP to EN 60 529	IP 54 in conjunction with solid gland plate top and bottom
Customs tariff number	94032080
EAN	4028177994041