
Rittal - The System.

Faster – better – everywhere.





KX 1541.000

KX terminal box, carbon steel with flange

State: 11/4/2025 (Source: rittal.com/us-en)



KX 1541.000 - KX terminal box, carbon steel with flange

The small enclosure KX, terminal box KX, with a gland plate allows for flexible interior installation and simple cable entry with optimum use of space.







Features

Model No.	KX 1541.000
Material	Housing: Carbon steel Cover: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with cover Mini-fasteners Carbon steel flange plates with seals and assembly components
Protection category NEMA	NEMA 1 NEMA 12
Protection category IP to EN 60 529	IP 55
Type rating according to UL 50E	Type 1 Type 12
IK code	IK08

© Rittal 2025 2

Features

Dimensions	Width: 800 mm
	Height: 400 mm
	Depth: 120 mm
	Width: 31.5 "
	Height: 15.7 ″
	Depth: 4.72 "
Material thickness - cover	1.25 mm
	0.05 ″
Material thickness - enclosure	1.25 mm
	0.05 ″
Flange Plates	: 1 + 1
	: 3 + 3
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	10.541
Gross weight	11.65
PCF/VE (cradle-to-gate)	44.6 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	84879059
EAN	4028177816466
E-Number Sweden	E3465212
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

© Rittal 2025 3

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Certificates	Protection category
Explanations	Declaration of conformity
	Declaration of conformity UK
	PCF-declaration

© Rittal 2025