

# Rittal – The System.

Faster – better – everywhere.



## SZ 2311.250

## Spacers

State: 6/27/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2311.250 - Spacers

Universal assembly component for all situations where spacing to the mounting level is required.

## Features

Model No.	SZ 2311.250
Product description	Utilized to mount components at an offset from mounting panel surface.
Technical specifications	With self-tapping thread for Ø 4.5 mm holes
Material	Hexagonal steel (SW8)
Surface finish	Zinc-plated
Length	50 mm 1.97 "
Mounting tip	On the rear, 5.5 x 13 carbon steel screws can be used, for example to fix top hat/support profile rails, contact hazard protection covers, main switch trim panels, and cable clamp rails, etc.
Packaging unit	12 pc(s).
Net weight	0.228 kg
Gross weight	0.244 kg
PCF/VE (cradle-to-gate)	0.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73181535
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234
Product description	SZ Spacer, L: 50 mm