


Rittal – The System.

Faster – better – everywhere.



SZ 2311.250 Spacers

State: 12/13/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2311.250 - Spacers

Universal assembly component for all situations where spacing to the mounting level is required.

Features

Model No.	SZ 2311.250
Product description	Utilized to mount components at an offset from mounting panel surface.
Technical specifications	With self-tapping thread for Ø 4.5 mm holes
Material	Hexagonal steel (SW8)
Surface finish	Zinc-plated
Length	50 mm 1.97 ~
Mounting tip	On the rear, 5.5 x 13 carbon steel screws can be used, for example to fix top hat/support profile rails, contact hazard protection covers, main switch trim panels, and cable clamp rails, etc.
Packaging unit	12 pc(s).
Net weight	0.228
Gross weight	0.244
PCF/VE (cradle-to-gate)	0.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73181535
EAN	4028177526822
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234