Rittal – The System.

Faster – better – everywhere.



KX 1550.000

E-box KX, carbon steel

State: 11/10/2026 (Source: www.rittal.com/us-en)

KX 1550.000 - E-box KX, carbon steel

The small enclosure KX, E-Box KX, carbon steel offers remarkable ease of assembly and flexibility when selecting lock systems.





Features

Model No.	KX 1550.000
Product description	The small enclosure KX, E-Box KX, carbon steel offers remarkable ease of assembly and flexibility when selecting lock systems.
Material	Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door Mounting panel Cam lock with 3 mm double-bit insert 180° hinge
Dimensions	Width: 200 mm Height: 400 mm Depth: 120 mm Width: 7.87 ″ Height: 15.7 ″ Depth: 4.72 ″

Features

Dimensions of mounting plate (W x H)	175 mm x 385 mm 6.89 ″ x 15.2 ″
Protection category IP to EN 60 529	IP 66
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Type rating according to 508A	Type 1 Type 3R Type 4 Type 12
IK code	IK08
Material thickness - enclosure	1.25 mm 0.05 ″
Material thickness - door	1.25 mm 0.05 ″
Material thickness – mounting plate	2 mm 0.08 ″
Lock	No. of locks: 1
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	4.288 kg
Gross weight	4.62 kg
PCF/VE (cradle-to-gate)	33.53 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Features

Product description	KX E-Box, WHD: 200x400x120 mm, sheet steel, with mounting plate, with door

Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
Certificates	Protection category
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK PCF-declaration