

Rittal – The System.

Faster – better – everywhere.



SG 2372.040

LED steady light component

State: 5/8/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2372.040 - LED steady light component for signal pillar, modular

With 360° signal transmission thanks to optimized prism system, number of potential stages = 5 components, with identical voltage.

Features

Model No.	SG 2372.040
Version	LED steady light component
Product description	With 360° signal transmission thanks to optimized prism system. Number of potential stages = 5 components, with identical voltage.
Benefits	Easy mounting and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colors and voltages.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.
Material	Housing of polyamide Cap: Transparent polycarbonate
Color	Blue
Diameter	70 mm 2.76 "
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Rated current max.	25 mA
Dimensions	Height: 56 mm Height: 2.2 "
Protection category IP to EN 60529	IP 54 if a cover or acoustic component is fitted at the top
Rated operating voltage	24 V (AC/DC)
Packaging unit	1 pc(s).

Features

Net weight	0.08
Gross weight	0.082
Customs tariff number	85311095
EAN	4028177220218
ETIM 9	EC000232
ETIM 8	EC000232
ECLASS 8.0	27371220

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------