

# Rittal – The System.

Faster – better – everywhere.



SG 2372.101

Signal pillar 3-fold LED

State: 1/19/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2372.101 - Signal pillar 3-fold LED

Rittal offers a flexible range of signal pillars for every application to instantaneously detect faults and operating states in machines and automated processes. The ready-to-connect three-way LED signal system is ideal if three standard signal colors are sufficient.

## Features

Model No.	SG 2372.101
Version	for conduit mounting
Benefits	Complete, ready-to-connect solution Extremely long service life of the LEDs (up to 100,000 hours, therefore maintenance-free) Minimal assembly work and warehousing costs
Technical specifications	3-stage, red, yellow, green Angle of projection: 3 x 120°
Cable entry	Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm Min. cable diameter: 0.12 “ Max. cable diameter: 0.26 “
Type of connection (electrical)	Clamp terminals
Light (bulb)	LEDs
Dimensions	Height: 211.5 mm Height: 8.33 “
Operating temperature range	-20 °C...50 °C -4 °F...122 °F
Protection category IP to EN 60 529	IP 65
Rated operating voltage	24 V
Thread	M12 x 1.5
Packaging unit	1 pc(s).
Net weight	0.25

# Features

---

Gross weight 0.308

---

Customs tariff number 85318070

---

EAN 4028177953758

---

ETIM 9 EC001042

---

ETIM 8 EC001042

---

ECLASS 8.0 27371230