

Rittal – The System.

Faster – better – everywhere.



SM 2384.040 Pushbutton Housings

State: 8/24/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SM 2384.040 - Pushbutton Housings Stainless steel

Switch housing of stainless steel 1.4301, (AISI 304), with Ø 22.5 mm switch cut-outs. Protection category IP 66.

Features

Model No.	SM 2384.040
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Housing and cover: Brushed, grain 240
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66
IK code	IK08
Dimensions	Width: 280 mm Height: 100 mm Depth: 90 mm Width: 11 " Height: 3.94 " Depth: 3.54 "
Material thickness - cover	1.25 mm 0.05 "
Material thickness - enclosure	1.25 mm 0.05 "
Hole pattern	60 mm 2.36 "
Breakouts (number x Ø)	4 x 22.5 mm 0.89 "
Lock	Lock version: Quick-release fasteners including plastic bushings No. of locks: 4

Features

Cable entry (quantity x diameter)	4
No. of metric knockouts	4
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	1.4
Gross weight	1.501
Customs tariff number	94039910
EAN	4028177529441
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---