

Rittal – The System.

Faster – better – everywhere.



KX 1562.000 KX terminal box

State: 4/17/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1562.000 - KX terminal box Stainless steel

The KX small enclosure stainless steel offers maximum data quality and consistency in engineering, flexibility, and safety for a variety of applications.



Features

Model No.	KX 1562.000
Product description	System perfection. The new small enclosure KX, stainless steel offers maximum data quality and consistency in engineering, flexibility, and safety for a variety of applications.
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Housing and cover: Brushed, grain 180
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 1 NEMA 3R NEMA 3RX NEMA 4 NEMA 4X NEMA 12
Protection category IP to EN 60529	IP 66

Features

Type rating according to UL 50E	Type 1 Type 3R Type 3RX Type 4 Type 4X Type 12
Dimensions	Width: 200 mm Height: 200 mm Depth: 80 mm Width: 7.87 " Height: 7.87 " Depth: 3.15 "
Material thickness - cover	1.25 mm 0.05 "
Material thickness - enclosure	1.25 mm 0.05 "
Lock	No. of locks: 4
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	1.68 kg
Gross weight	1.926 kg
Customs tariff number	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	KX Terminal box, WHD: 200x200x80 mm, stainless steel 1.4301, without mounting plate, with cover, with quick-release fasteners

Approvals

Approvals

Approvals

Bureau Veritas
DNV-GL
Lloyds Register of Shipping
UL + C-UL (listed)

Explanations

Declaration of conformity
PCF-declaration