

Rittal – The System.

Faster – better – everywhere.



HD 2410.011 Cable gland HD

State: 4/20/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 2410.011 - Cable gland HD

The design is more compact and the locknut is already included.



Features

| | |
|---------------------|--|
| Model No. | HD 2410.011 |
| Version | Standard |
| Benefits | Smooth, solid exterior surfaces effectively prevent the accumulation of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands. |
| Applications | Production and packaging of food and beverages Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry |
| Material | Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600 |
| Supply includes | Incl. lock nut |
| Dimensions | Thread: M16 x 1.5 |
| For cable diameters | 5 - 10 mm 0.2 - 0.39 " |

Features

| | |
|-------------------------------------|---|
| Operating temperature range | -20 °C...100 °C -4 °F...212 °F |
| Protection category IP to IEC 60529 | IP69 / IPX8 (5 bar, 30 min) |
| Packaging unit | 5 pc(s). |
| Net weight | 0.1 kg |
| Gross weight | 0.2 kg |
| Customs tariff number | 73072980 |
| ETIM 9 | EC000441 |
| ETIM 8 | EC000441 |
| ECLASS 8.0 | 27149109 |
| Product description | HD Cable gland, stainless steel 1.4305, size: M16x1,5, for cables Ø 5-10 mm, Standard version |

Approvals

| | |
|-----------|-------------------------------|
| Approvals | UR + C-UR (recognized) VDE |
|-----------|-------------------------------|