# Rittal - The System.

Faster – better – everywhere.





EB 1579.500 E-Box EB

State: 11/9/2025 (Source: rittal.com/us-en)



#### EB 1579.500 - E-Box EB

Wall-mounted housing with door and mounting plate made from sheet steel. Protection category IP 66. With 180° hinge. Lock insert may be exchanged for individual lock systems.

### **Features**

Model No.	EB 1579.500
Material	Housing and door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door 180° hinge Cam lock with 3 mm double-bit insert Mounting panel
Protection category NEMA	NEMA 4
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 300 mm  Height: 800 mm  Depth: 155 mm  Width: 11.8 "  Height: 31.5 "  Depth: 6.1 "
Dimensions of mounting plate (W x H)	275 mm x 785 mm 10.8 ″ x 30.9 ″
Material thickness - enclosure	1.38 mm 0.05 ″
Material thickness - door	1.25 mm 0.05 ″

© Rittal 2025

### **Features**

Material thickness – mounting plate	2 mm 0.08 "
Lock	Lock version: Cam
	No. of locks: 2
	Lock Insert: 3 mm double-bit
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	12.145
Gross weight	12.784
Customs tariff number	94032080
EAN	4028177251823
E-Number Sweden	E3404514
ECLASS 8.0	27180101

## **Approvals**

Approvals	C-UL
	UL
	UL + C-UL (listed)
Explanations	Manufacturer's declaration
	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3