


Rittal – The System.

Faster – better – everywhere.



SZ 2411.811

Cable gland, brass

State: 9/8/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.811 - Cable gland, brass

Integrated clamping membranes ensure safe tightening and cable-friendly strain relief.

Features

Model No.	SZ 2411.811
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief that protects the cables
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
Protection category IP to IEC 60529	IP 68 (5 bar, 30 min.)
Dimensions	Height: 28 mm Height: 1.1 "
Thread	M16 x 1.5
Thread length	7 mm 0.28 "
Min. cable diameter	5 mm 0.2 "
Max. cable diameter	10 mm 0.39 "
Operating temperature range	-40 °C...100 °C -40 °F...212 °F
torque	9 Nm
Width across flats	20 mm
Dimensions	Thread: M16 x 1.5 Thread length: 7 mm Thread: M16 x 1.5 Thread length: 0.28 "

Features

Type rating according to UL 50E	Type 4X
Packaging unit	15 pc(s).
Net weight	0.3
Gross weight	0.451
Customs tariff number	74198090
EAN	4028177810082
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

Approvals

Approvals	UR + C-UR (recognized) VDE
Explanations	Declaration of conformity Declaration of conformity UK