

Rittal – The System.

Faster – better – everywhere.



SZ 2411.851

Cable gland, brass

State: 4/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.851 - Cable gland, brass

Integrated clamping membranes ensure safe tightening and cable-friendly strain relief.

Features

| | |
|-------------------------------------|---|
| Model No. | SZ 2411.851 |
| Benefits | Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief that protects the cables |
| Material | Brass Seal: CR/NBR |
| Surface finish | Nickel-plated |
| Protection category IP to IEC 60529 | IP 68 (5 bar, 30 min.) |
| Dimensions | Height: 43 mm Height: 1.69 " |
| Thread | M40 x 1.5 |
| Thread length | 9 mm 0.35 " |
| Min. cable diameter | 19 mm 0.75 " |
| Max. cable diameter | 28 mm 1.1 " |
| Operating temperature range | -40 °C...100 °C -40 °F...212 °F |
| torque | 17 Nm |
| Width across flats | 43 mm |
| Dimensions | Thread: M40 x 1.5 Thread length: 9 mm Thread: M40 x 1.5 Thread length: 0.35 " |

Features

| | |
|---------------------------------|---|
| Type rating according to UL 50E | Type 1 Type 4 Type 4X Type 12 Type 13 |
| Packaging unit | 4 pc(s). |
| Net weight | 0.64 kg |
| Gross weight | 0.692 kg |
| Customs tariff number | 74198090 |
| ETIM 9 | EC000441 |
| ETIM 8 | EC000441 |
| ECLASS 8.0 | 27149109 |
| Product description | SZ Cable gland, brass, size: M40x1,5, for cables ø 19-28 mm |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) VDE |
| Explanations | Declaration of conformity Declaration of conformity UK |
