Rittal – The System.

Faster – better – everywhere.



SZ 2486.600

Metal multi-tooth screws

State: 11/1/2026 (Source: www.rittal.com/us-en)

SZ 2486.600 - Metal multi-tooth screws

Multi-tooth drive for optimum transmission of torques, extended tool life and increased safety and reliability when tightening and loosening screw connections.

Features

Model No.	SZ 2486.600
Version	Metal multi-tooth screws
Product description	Multi-tooth drive for optimum transmission of torques, extended tool life and increased safety and reliability when tightening and loosening screw connections.
Applications	For Ø 4.5 or 4.7 mm round holes in the enclosure profile, punched rails and punched section without mounting flange
Dimensions	Thread: 5.5 Thread length: 13 mm Thread: 5.5 Thread length: 0.51 ″
Thread	5.5
Packaging unit	300 pc(s).
Net weight	0.9 kg
Gross weight	1.055 kg
Customs tariff number	73181900
ETIM 9	EC000889
ETIM 8	EC000889
ECLASS 8.0	23110112
Product description	VX Metal multi-tooth screw, for sheet steel, size: 5.5x13 mm

© Rittal 2026