

Rittal – The System.

Faster – better – everywhere.



BG 1611.510

BG Bus Housings

State: 1/26/2026 (Source: ittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

BG 1611.510 - BG Bus Housings

Wall-mounted enclosure with door of carbon steel, with polycarbonate viewing window. Protection category IP 65. Bus modules of virtually all makes may be attached.

Features

Model No.	BG 1611.510
Material	Housing: Carbon steel Door: Carbon steel Viewing window: Polycarbonate, 4 mm1
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with door Viewing window in the door
Protection category NEMA	NEMA 12
Protection category IP to EN 60 529	IP 65
IK code	IK08
Dimensions	Width: 400 mm Height: 500 mm Depth: 160 mm Width: 15.7 " Height: 19.7 " Depth: 6.3 "
Material thickness - enclosure	1.38 mm 0.05 "
Material thickness - door	1.5 mm 0.06 "
Position door catch	right
Number of support rails	3
Breakouts (number x Ø)	33

Features

Lock	Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit
Cable entry (quantity x diameter)	33 x M20
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	7.39
Gross weight	7.779
Customs tariff number	94032080
EAN	4028177251878
ECLASS 8.0	27180101

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
