Rittal – The System.

Faster – better – everywhere.





SZ 2500.200 LED system light

State: 11/3/2025 (Source: rittal.com/us-en)



SZ 2500.200 - LED system light

LED system light - the first light designed especially for enclosures! Advanced LED technology provides even more light into the last recess.





Features

Model No.	SZ 2500.200
Version	without socket
Benefits	Optimum illumination of the entire enclosure
	Option of clip-on, screw or magnetic attachment
	A configuration to suit every application
Version	without socket
	90° rotating connector
	Adjustable light distribution
Material	Light body: Extruded aluminum
	Light cover: polycarbonate
	Light ends: PC-ABS
Color	Enclosure: RAL 7016
Supply includes	Assembly screws
Rated power	11 W
Connection options	Power Supply, 3-pole
	Through-wiring, 3-pole
	Door-operated switch
Overvoltage category	II

© Rittal 2025

Features

Protection category	II (total insulation)
Light – installation type	Screw fastening Clip fastening Magnetic fastener (accessories)
Rated impulse withstand voltage, phase to earth	2500 V AC
Rated insulation voltage	300 V AC
Installation options	Directly onto the enclosure section with 25 mm pitch pattern
Luminous flux	900 lm
Light color	4000 K (neutral white)
Note	Connection accessories should be ordered separately
Dimensions	Width: 437 mm Height: 75 mm Depth: 23 mm Width: 17.2 " Height: 2.95 " Depth: 0.91 "
Operating temperature range	-20 °C55 °C -4 °F131 °F
Rated operating voltage	100 V - 230 V, 1~, 50 Hz/60 Hz
Protection category IP to IEC 60 529	IP 20
Packaging unit	1 pc(s).
Net weight	0.426
Gross weight	0.56
Customs tariff number	94054990
EAN	4028177806955
ETIM 9	EC000321
ETIM 8	EC000321
ECLASS 8.0	27189241

© Rittal 2025 3

Approvals

Approvals	cqc-ccc
	ENEC
	UL
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 4