

Rittal – The System.

Faster – better – everywhere.



SZ 2500.213 LED system light

State: 8/15/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2500.213 - LED system light

LED system light - the first light designed especially for enclosures! Advanced LED technology provides even more light into the last recess.



Features

Model No.	SZ 2500.213
Version	with socket
Benefits	Optimum illumination of the entire enclosure Option of clip-on, screw or magnetic attachment A configuration to suit every application
Version	Socket 90° rotating connector Adjustable light distribution
Material	Light body: Extruded aluminum Light cover: polycarbonate Light ends: PC-ABS
Color	Enclosure: RAL 7016
Supply includes	Assembly screws
Rated power	11 W
Connection options	Power Supply, 3-pole Through-wiring, 3-pole Door-operated switch
Overvoltage category	II

Features

Protection category	II (total insulation)
Light – installation type	Screw fastening Clip fastening
Rated impulse withstand voltage, phase to earth	2500 V AC
Rated insulation voltage	300 V AC
Installation options	Directly onto the enclosure section with 25 mm pitch pattern
Luminous flux	900 lm
Light color	4000 K (neutral white)
Note	Connection accessories should be ordered separately
Dimensions	Width: 437 mm Height: 80 mm Depth: 44 mm Width: 17.2 " Height: 3.15 " Depth: 1.73 "
Operating temperature range	-20 °C...55 °C -4 °F...131 °F
Outlets	CH (type J, SEV 1011)
Rated operating voltage	100 V - 230 V, 1~, 50 Hz/60 Hz
Socket version	CH (type J, SEV 1011)
Protection category IP to IEC 60529	IP 20
Packaging unit	1 pc(s).
Net weight	0.6
Gross weight	0.62
Customs tariff number	94054990
EAN	4028177811331
ETIM 9	EC000321
ETIM 8	EC000321

Features

ECLASS 8.0	27189241
------------	----------

Approvals

Approvals	CQC-CCC ENEC
-----------	-----------------

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---