

Rittal – The System.

Faster – better – everywhere.



SZ 2500.220 LED system light

State: 8/4/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2500.220 - LED system light

LED system light - the first light designed especially for enclosures! Advanced LED technology provides even more light into the last recess.



Features

| | |
|---------------------|--|
| Model No. | SZ 2500.220 |
| Version | without socket |
| Benefits | Optimum illumination of the entire enclosure Option of clip-on, screw or magnetic attachment A configuration to suit every application |
| Version | 90° rotating connector Adjustable light distribution |
| Material | Light body: Extruded aluminum Light cover: polycarbonate Light ends: PC-ABS |
| Color | Enclosure: RAL 7016 |
| Supply includes | Assembly screws |
| Rated power | 11 W |
| Connection options | Power Supply, 2-pole Through-wiring, 2-pole Door-operated switch |
| Protection category | III (SELV) |

Features

| | |
|-------------------------------------|--|
| Light – installation type | Screw fastening Clip fastening Magnetic fastener (accessories) |
| Installation options | Directly onto the enclosure section with 25 mm pitch pattern |
| Luminous flux | 900 lm |
| Light color | 4000 K (neutral white) |
| Note | Connection accessories should be ordered separately |
| Dimensions | Width: 437 mm Height: 75 mm Depth: 23 mm Width: 17.2 " Height: 2.95 " Depth: 0.91 " |
| Operating temperature range | -20 °C...55 °C -4 °F...131 °F |
| Rated operating voltage | 24 V (DC) |
| Protection category IP to IEC 60529 | IP 20 |
| Packaging unit | 1 pc(s). |
| Net weight | 0.394 |
| Gross weight | 0.52 |
| Customs tariff number | 94054990 |
| EAN | 4028177806979 |
| ETIM 9 | EC000321 |
| ETIM 8 | EC000321 |
| ECLASS 8.0 | 27189241 |

Approvals

Approvals

Approvals

CQC
CQC-CCC
ENEC
UL + C-UL (listed)

Explanations

Declaration of conformity
Declaration of conformity UK