

Rittal – The System.

Faster – better – everywhere.



TP 2683.600

One-piece consoles

State: 5/9/2024 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 2683.600 - One-piece consoles Stainless steel

Console made from stainless steel 1.4301, (AISI 304), ready-to-use unit with high protection category IP 55 in four different widths. Easy handling thanks to self-locking lid stay. Interchangeable lock insert. Easy cable entry thanks to split base plates.

Features

Model No.	TP 2683.600
Material	Housing: Stainless steel 1.4301 (AISI 304), 1.5 mm Door or double door and console lid: Stainless steel 1.4301 (AISI 304), 2.0 mm Mounting plate: Carbon steel, 3.0 mm
Surface finish	Housing, door, console lid and base plates: Brushed, grain 400 Mounting plate: Zinc-plated
Supply includes	Housing, solid back and sides Door or double door at front, with locking rod Console lid with lid stay and cam lock latched in the enclosure Locks with double-bit insert Base plates, divided Mounting plate
Dimensions	Width: 600 mm Height: 960 mm Width: 23.6 " Height: 37.8 "
Dimensions of mounting plate (W x H)	530 mm x 780 mm 20.9 " x 30.7 "
Top depth	480 mm 18.9 "
Bottom depth	400 mm 15.7 "
Number of doors	1
Protection category IP to IEC 60529	IP 55
Protection category NEMA	NEMA 12

Features

Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Weight/packaging unit	52 kg 114.6 lb.
Customs tariff number	94032080
EAN	4028177031319
ETIM 7.0	EC000784
ECLASS 8.0	27180504

Approvals

Approvals	TÜV UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK