

Rittal – The System.

Faster – better – everywhere.



TP 2686.600 One-piece consoles

State: 5/21/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 2686.600 - One-piece consoles Stainless steel

Console made from stainless steel 1.4301, (AISI 304), ready-to-use unit with high protection category IP 55 in four different widths. Easy handling thanks to self-locking lid stay. Interchangeable lock insert. Easy cable entry thanks to split base plates.



Features

Model No.	TP 2686.600
Material	Housing: Stainless steel 1.4301 (AISI 304), 1.5 mm Door or double door and console lid: Stainless steel 1.4301 (AISI 304), 2.0 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Housing, door, console lid and base plates: Brushed, grain 400 Mounting panel: Zinc-plated
Supply includes	Housing, solid back and sides Door or double door at front, with locking rod Console lid with lid stay and cam lock latched in the enclosure Locks with double-bit insert Base plates, divided Mounting panel
Dimensions	Width: 1,200 mm Height: 960 mm Width: 47.2 " Height: 37.8 "
Dimensions of mounting plate (W x H)	1,130 mm x 780 mm 44.5 " x 30.7 "

Features

Top depth	480 mm 18.9 "
Bottom depth	400 mm 15.7 "
Number of doors	2
Protection category IP to IEC 60529	IP 55
Protection category NEMA	NEMA 12
Base material	Stainless steel 1.4301 (AISI 304)
Dimensions	Width: 1,200 mm Height: 960 mm Top depth: 480 mm Bottom depth: 400 mm Width: 47.2 " Height: 37.8 " Top depth: 18.9 " Bottom depth: 15.7 "
Packaging unit	1 pc(s).
Net weight	83.1 kg
Gross weight	90.3 kg
Customs tariff number	94032080
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504
Product description	TP one-piece console, WHD: 1200x960x400/D2: 480 mm, stainless steel, 1.4301

Approvals

Approvals	TÜV UL + C-UL (listed)
-----------	---------------------------

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK