
Rittal – The System.

Faster – better – everywhere.



AX 2830.102

Base/plinth panels, front and rear


State: 11/15/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AX 2830.102 - Base/plinth panels, front and rear for AX

The base/plinth panels at the front and rear offer a large opening for optimal access to the screw-fastening point and simple cable routing.



Features

Model No.	AX 2830.102
Material	Base/plinth trim panels, front/rear: Carbon steel
Color	RAL 9005
Supply includes	1 base/plinth trim panel, front/rear, 200 mm 2 x base/plinth trim panels, front/rear, 100 mm high
Note	Base/plinth elements are required on the sides to finish off a base/plinth unit
Dimensions	Height: 200 mm Height: 7.87 ″
Suitable for	Enclosure type: AX Width: = 1,000 mm Enclosure type: AX Width: = 39.4 ″
Packaging unit	2 pc(s).
Net weight	4.8 kg
Gross weight	4.924 kg
Customs tariff number	94039910
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Features

Product description	AX base/plinth trim panel, front and rear, H: 200 mm, for W: 1,000 mm

Approvals

Approvals	UL + C-UL - FTTA