Rittal - The System.

Faster – better – everywhere.





AX 2262.130 AX wall-mounted housing, 3-part


State: 12/7/2025 (Source: rittal.com/us-en)



AX 2262.130 - AX wall-mounted housing, 3-part

The delivery concept of the three-part AX wall-mounted enclosure reduces complexity and increases flexibility. Thanks to the AX/VX modular system, the enclosures are suitable for various applications. The three-part structure ensures easy access.







Features

Model No.	AX 2262.130
Version	Wall-mounted housing IT
Material	Wall and hinged part: Carbon steel, 1.5 mm
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	Wall and hinged part: RAL 7035
	Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section: Flange (gland) plate, solid, top and bottom
	Hinged part with 25 mm pitch pattern in the front and rear frame,
	two 19" profile angles at the front, fixed in place
	Designer viewing door
	Center part lock: 3 mm double bit
	Lock design – glazed door: Security lock 3524 E
	Comfort handle for lock inserts and 2-point locking
Height units	21 U

© Rittal 2025 2

Features

Dimensions Width: 600 mm Height: 1,012 mm Depth: 373 mm Width: 23.6 " Height: 39.8 " Depth: 14.7 " Installation depth 320 mm 12.6 " Clearance width: 502 mm Clearance height: 951 mm Clearance width: 19.8 " Clearance height: 37.4 " Depth hinged part 216 mm 8.5 " Depth of wall section 135 mm 5.31 " No. of locks 1 Load capacity of hinged part (static) Load capacity wall section (static) Dase material Carbon steel Lock Lock version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 529 Packaging unit 1 pc(s). Net weight 43 Gross weight 44 Information regarding the PCF class Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080 EAN 4028177983328		
Clearances Clearance width: 502 mm Clearance height: 951 mm Clearance height: 951 mm Clearance height: 37.4 " Depth hinged part 216 mm 8.5 " Depth of wall section 135 mm 5.31 " No. of locks 1 Load capacity of hinged part (static) Load capacity wall section (static) Load capacity wall section (static) Lock Lock version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 Packaging unit 1 pc(s). Net weight 43 Gross weight 44 Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately or class the basis of the product weight and self-declared Customs tariff number 94032080	Dimensions	Height: 1,012 mm Depth: 373 mm Width: 23.6 " Height: 39.8 "
Clearance height: 951 mm Clearance width: 19.8 " Clearance height: 37.4 " Depth hinged part 216 mm 8.5 " Depth of wall section 135 mm 5.31 " No. of locks 1 Load capacity of hinged part (static) Load capacity wall section (static) Carbon steel Lock Lock version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 1 p 54 in conjunction with solid gland plate top and bottom 1 pc(s). Net weight 43 Gross weight 44 Information regarding the PCF class of the product weight and self-declared Customs tariff number 94032080	Installation depth	
B.5 ° Depth of wall section 135 mm 5.31 ° No. of locks 1 Load capacity of hinged part (static) Load capacity wall section (static) 250 N Base material Carbon steel Lock Lock version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 IP 54 in conjunction with solid gland plate top and bottom 529 Packaging unit 1 pc(s). Net weight 43 Gross weight 44 Information regarding the PCF category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	Clearances	Clearance height: 951 mm Clearance width: 19.8 ″
No. of locks 1 Load capacity of hinged part (static) Load capacity wall section (static) 250 N Base material Carbon steel Lock Lock version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 IP 54 in conjunction with solid gland plate top and bottom 529 Packaging unit 1 pc(s). Net weight 43 Gross weight 44 Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	Depth hinged part	
Load capacity of hinged part (static) Load capacity wall section (static) Base material Carbon steel Lock Lock version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 IP 54 in conjunction with solid gland plate top and bottom 529 Packaging unit 1 pc(s). Net weight 43 Gross weight 44 Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	Depth of wall section	
(static) Load capacity wall section (static) 250 N Base material Carbon steel Lock Lock version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 IP 54 in conjunction with solid gland plate top and bottom 529 Packaging unit 1 pc(s). Net weight 43 Gross weight 44 Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	No. of locks	1
Base material Carbon steel Lock Lock version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 IP 54 in conjunction with solid gland plate top and bottom 529 Packaging unit 1 pc(s). Net weight 43 Gross weight 44 Information regarding the PCF class Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080		750 N
Lock Version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 529 Packaging unit 1 pc(s). Net weight 43 Gross weight 44 Information regarding the PCF class the basis of the product weight and self-declared Customs tariff number 94032080	Load capacity wall section (static)	250 N
Lock Insert: Security lock insert no. 3524 E Protection category IP to EN 60 IP 54 in conjunction with solid gland plate top and bottom Packaging unit 1 pc(s). Net weight 43 Gross weight Information regarding the PCF category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	Base material	Carbon steel
Packaging unit 1 pc(s). Net weight 43 Gross weight 44 Information regarding the PCF category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	Lock	•
Net weight Gross weight 44 Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	· •	IP 54 in conjunction with solid gland plate top and bottom
Gross weight Information regarding the PCF class Customs tariff number 44 Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared 94032080	Packaging unit	1 pc(s).
Information regarding the PCF Category B: PCF value (cradle-to-gate) calculated approximately of the basis of the product weight and self-declared Customs tariff number 94032080	Net weight	43
class the basis of the product weight and self-declared Customs tariff number 94032080	Gross weight	44
		Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
EAN 4028177983328	Customs tariff number	94032080
	EAN	4028177983328

© Rittal 2025 3

Features

ETIM 9	EC002500	
ETIM 8	EC002500	
ECLASS 8.0	27180101	

Approvals

Explanations Declaration of conformity

© Rittal 2025