

Rittal – The System.

Faster – better – everywhere.



AX 2262.155

AX wall-mounted housing, 3-part

State: 2/28/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2262.155 - AX wall-mounted housing, 3-part with Blue e+ outlet filter

The delivery concept of the three-part AX wall-mounted enclosures reduces complexity and increases flexibility. Thanks to the AX/VX modular system, the enclosures are suitable for various applications. The three-part structure ensures easy access.



Features

Model No.	AX 2262.155
Version	Wall-mounted housing IT
Material	Wall and hinged part: Carbon steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	Wall and hinged part: RAL 7035 Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section: Flange (gland) plate, solid, top and bottom Hinged part with 25 mm pitch pattern in the front and rear frame, two 19" profile angles at the front, fixed in place Designer viewing door Lock design – glazed door: Security lock 3524 E Center part lock: 3 mm double bit 2 Blue e+ outlet filters 3238.300 (enclosed loose) Comfort handle for lock inserts and 2-point locking
Height units	21 U

Features

Dimensions	Width: 600 mm Height: 1,012 mm Depth: 573 mm Width: 23.6 " Height: 39.8 " Depth: 22.6 "
Installation depth	520 mm 20.5 "
Clearances	Clearance width: 502 mm Clearance height: 951 mm Clearance width: 19.8 " Clearance height: 37.4 "
Depth hinged part	416 mm 16.4 "
Depth of wall section	135 mm 5.31 "
No. of locks	1
IK code	IK08
Load capacity of hinged part (static)	750 N
Load capacity wall section (static)	250 N
Base material	Carbon steel
Lock	Lock version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E
Protection category IP to EN 60529	IP 54 in conjunction with solid gland plate top and bottom
Customs tariff number	94032080
Product description	AX wall-mounted enclosure, 3-part, W x H x D: 600 x 1012 x 573 mm, 21 U, wall part: closed flange plate top and bottom, with comfort handle

Approvals

Explanations

Declaration of conformity