



SK 3105.400 - Enclosure Heater with fan

Enclosure heaters to regulate relative humidity, prevent temperatures from dropping below the dew point and stop condensation forming inside the enclosure. This prevents consequential damage associated with corrosion or electrical short circuits. Version with fan. Continuous thermal output 235 – 800 W.



Features

| | |
|---------------------------|--|
| Model No. | SK 3105.400 |
| Product description | Enclosure heaters to regulate relative humidity, prevent temperatures from dropping below the dew point and stop condensation forming inside the enclosure. This prevents consequential damage associated with corrosion or electrical short circuits. |
| Material | Aluminum, anodized |
| Supply includes | PTC heater with fan Fasteners |
| Continuous thermal output | Continuous thermal output with fan |
| Integrated fan | Yes |
| Note | A thermostat is recommended for precise temperature control inside the enclosure In order to prevent condensation on assemblies, hygostat is recommended to regulate heating In larger enclosures, even heat distribution is best achieved by installing several low-output heaters. |

Features

| | |
|-------------------------------------|--|
| Note on Model No.: | Operation at a temperature of -40 °C is possible. Upon request, you will receive a manufacturer's declaration. |
| Continuous thermal output at 10 °C | 800 W - 870 W 2,730 BTU/h - 2,969 BTU/h |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Dimensions | Width: 103 mm Height: 200 mm Depth: 103 mm Width: 4.06 " Height: 7.87 " Depth: 4.06 " |
| Pre-fuse | Miniature circuit-breaker/fuse: 6 A |
| Protection category IP to IEC 60529 | IP 20 |
| Protection category | II (total insulation) |
| Operating temperature range | -33 °C...65 °C -27 °F...149 °F |
| Packaging unit | 1 pc(s). |
| Net weight | 1.1 kg |
| Gross weight | 1.2 kg |
| Customs tariff number | 85162999 |
| ETIM 9 | EC000737 |
| ETIM 8 | EC000737 |
| ECLASS 8.0 | 27180710 |
| Product description | SK switch cabinet heater, with fan, 800/870 W, 230 V, 1~, 50/60 Hz, W x H x D: 103 x 200 x 103 mm |

Approvals

Approvals

Approvals

CSA

UR + C-UR (recognized)

Explanations

Declaration of conformity

Declaration of conformity UK