


# Rittal – The System.

Faster – better – everywhere.



## SZ 2370.530 LED flashing light component

State: 7/11/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2370.530 - LED flashing light component for signal pillar, modular

With 360° signal transmission thanks to optimized prism system, no. of potential stages = 5 components, with identical voltage.

## Features

Model No.	SZ 2370.530
Version	LED flashing light component
Product description	With 360° signal transmission thanks to optimized prism system. Number of potential stages = 5 components, with identical voltage.
Benefits	Easy mounting and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colors and voltages. Flashing and stroboscopic light element incl. lamp, suitable for direct use.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.
Material	Housing of polyamide Cap: Transparent polycarbonate
Color	Clear
Diameter	70 mm 2.76 "
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Dimensions	Height: 56 mm Height: 2.2 "
Protection category IP to EN 60529	IP 54 if a cover or acoustic component is fitted at the top
Rated operating voltage	24 V (AC/DC)

# Features

Packaging unit	1 pc(s).
Net weight	0.07
Gross weight	0.083
Customs tariff number	94054990
EAN	4028177656482
ECLASS 8.0	27371220

# Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------