
Rittal – The System.

Faster – better – everywhere.





SG 2371.020 Flashing light component

State: 11/20/2025 (Source: rittal.com/us-en)



SG 2371.020 - Flashing light component for signal pillar, modular

With 360° signal transmission thanks to optimized prism system, no. of potential stages = 5 components, with identical voltage.

Features

Model No.	SG 2371.020
Version	Flashing light component
Product description	With 360° signal transmission thanks to optimized prism system. Number of potential stages = 5 components, with identical voltage.
Benefits	Easy mounting and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colors and voltages. Flashing and stroboscopic light element incl. lamp, suitable for direct use.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.
Material	Housing of polyamide Cap: Transparent polycarbonate
Color	Yellow
Diameter	70 mm 2.76 ″
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Rated current max.	125 mA
Dimensions	Height: 56 mm Height: 2.2 ″
Protection category IP to EN 60 529	IP 54 if a cover or acoustic component is fitted at the top

© Rittal 2025

2

Features

Rated operating voltage	24 V (DC)
Packaging unit	1 pc(s).
Net weight	0.09
Gross weight	0.098
Customs tariff number	85311095
EAN	4028177220096
ETIM 9	EC000232
ETIM 8	EC000232
ECLASS 8.0	27371220

Approvals

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3