

# Rittal – The System.

Faster – better – everywhere.



## SM 2384.010 Pushbutton Housings

State: 7/11/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SM 2384.010 - Pushbutton Housings Stainless steel

Switch housing of stainless steel 1.4301, (AISI 304), with Ø 22.5 mm switch cut-outs. Protection category IP 66.

## Features

|                                    |   |
|------------------------------------|---|
| Model No.                          | SM 2384.010   |
| Material                           | Housing: Stainless steel 1.4301 (AISI 304)<br>Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish                     | Housing and cover: Brushed, grain 240   |
| Supply includes                    | Housing with cover<br>Quick-release fasteners including plastic bushings  |
| Protection category NEMA           | NEMA 4X   |
| Protection category IP to EN 60529 | IP 66   |
| IK code                            | IK08  |
| Dimensions                         | Width: 100 mm<br>Height: 100 mm<br>Depth: 90 mm<br>Width: 3.94 "<br>Height: 3.94 "<br>Depth: 3.54 "                 |
| Material thickness - cover         | 1.25 mm<br>0.05 "   |
| Material thickness - enclosure     | 1.25 mm<br>0.05 "   |
| Hole pattern                       | 60 mm<br>2.36 "   |
| Breakouts (number x Ø)             | 1 x 22.5 mm<br>0.89 "   |
| Lock                               | Lock version: Quick-release fasteners including plastic bushings<br>No. of locks: 2                                 |

# Features

---

|                                   |   |
|-----------------------------------|---|
| Cable entry (quantity x diameter) | 1   |
| No. of metric knockouts           | 1   |
| Base material                     | Stainless steel 1.4301 (AISI 304)   |
| Packaging unit                    | 1 pc(s).  |
| Net weight                        | 0.68 kg   |
| Gross weight                      | 0.72 kg   |
| PCF/VE (cradle-to-gate)           | 2.64  |
| Customs tariff number             | 84879090  |
| ETIM 9                            | EC000261  |
| ETIM 8                            | EC000261  |
| ECLASS 8.0                        | 27180101  |
| Product description               | SM Switch housing, WHD: 100x100x90 mm, Stainless steel 1.4301, without mounting plate, 1 switch cut-out |

# Approvals

---

|              |  |
|--------------|--|
| Explanations | Declaration of conformity<br>Declaration of conformity UK<br>PCF-declaration |
|--------------|--|