Rittal – The System.

Faster – better – everywhere.



SK 3110.000

Thermostat

State: 11/14/2026 (Source: www.rittal.com/us-en)

SK 3110.000 - Thermostat Internal Enclosure Thermostat

Suitable for controlling fan units, heaters, and heat exchangers. This thermostat can also be used as a signal generator for monitoring the internal enclosure temperature.

Features

Model No.	SK 3110.000
Product description	Suitable for controlling fan units, heaters and heat exchangers. This thermostat can also be used as a signal generator for monitoring the internal enclosure temperature.
Benefits	Time-saving connection technique using a terminal strip with a screw connection from the outside. Flexible mounting on a vertical or horizontal 35 mm support rail to EN 50 022, snap fastening in the enclosure section or on the mounting plate using the supplied adapter.
Technical specifications	Bi-metal controller as a temperature-sensitive element with thermal feedback Contact population: Single-pole change-over contact as a quick-break contact Permissible contact load: Category 5 – 3 (heating): AC 10 (4) A (inductive load at cos φ = 0.6) / category 5- 4 (cooling): AC 5 (4) A (inductive load at cos φ = 0.6) / DC = max. 30 W Switching difference: approx. 1 K ± 0.8 K.
Color	RAL 7035
Packaging unit	1 pc(s).
Dimensions	Width: 71 mm Height: 71 mm Depth: 33.5 mm Width: 2.8 ″ Height: 2.8 ″ Depth: 1.32 ″
Setting range	5 °C...60 °C 41 °F...140 °F
Rated operating voltage	24 V - 230 V, 1~ 24 V - 60 V (DC)

© Rittal 2026

Features

Net weight	0.095 kg
Gross weight	0.12 kg
Customs tariff number	90321020
ETIM 9	EC004587
ETIM 8	EC004587
ECLASS 8.0	27210707
Product description	SK Thermostat, enclosure internal thermostat, 24-230 V, 1~, 24-60 V (DC), Colour RAL 7035, WHD: 71 x 71 x 33.5 mm

Approvals

Approvals	UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK RoHS/REACH Additional Information