

Rittal – The System.

Faster – better – everywhere.



SM 2384.020 Pushbutton Housings

State: 6/10/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SM 2384.020 - Pushbutton Housings Stainless steel

Switch housing of stainless steel 1.4301, (AISI 304), with Ø 22.5 mm switch cut-outs. Protection category IP 66.

Features

Model No.	SM 2384.020
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Housing and cover: Brushed, grain 240
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66
IK code	IK08
Dimensions	Width: 160 mm Height: 100 mm Depth: 90 mm Width: 6.3 " Height: 3.94 " Depth: 3.54 "
Material thickness - cover	1.25 mm 0.05 "
Material thickness - enclosure	1.25 mm 0.05 "
Hole pattern	60 mm 2.36 "
Breakouts (number x Ø)	2 x 22.5 mm 0.89 "
Lock	Lock version: Quick-release fasteners including plastic bushings No. of locks: 4

Features

Cable entry (quantity x diameter)	2
No. of metric knockouts	2
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	0.98 kg
Gross weight	1 kg
PCF/VE (cradle-to-gate)	3.83
Customs tariff number	84879090
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	SM Switch housing, WHD: 160x100x90 mm, Stainless steel 1.4301, without mounting plate, 2 switch cut-outs

Approvals

Explanations	Declaration of conformity Declaration of conformity UK PCF-declaration
--------------	--