


Rittal – The System.

Faster – better – everywhere.



SZ 2388.050 Rail

State: 8/15/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2388.050 - Rail for EMC shielding bracket and strain relief

Combined rails for strain relief and EMC contacting of inserted cables.



Features

| | |
|----------------------|---|
| Model No. | SZ 2388.050 |
| Version | C rail to accommodate cable clamps T-head slots in 40 mm hole pattern for cable attachment using cable ties |
| Product description | Combined rails for strain relief and EMC contacting of inserted cables. |
| Benefits | Additional contacting on the left or right of the rail via existing holes (9 mm diameter) Prepared for tool-free assembly of EMC shielding bracket |
| Material | Extruded aluminum section |
| Surface finish | Chrome-free passivated |
| Supply includes | 1 rail 2 retaining brackets Assembly components |
| Length | 953 mm 37.5 " |
| Installation options | On the horizontal/vertical enclosure section on a mounting plate, may also be fitted without a retaining bracket |

Features

| | |
|-----------------------|--|
| Suitable for | Enclosure type: VX TS Width: = 1,000 mm Enclosure type: VX TS Width: = 39.4 ~ |
| Packaging unit | 1 pc(s). |
| Net weight | 0.76 |
| Gross weight | 0.84 |
| Customs tariff number | 76042990 |
| EAN | 4028177698932 |
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |