
Rittal – The System.

Faster – better – everywhere.





SZ 2388.650 Rail


State: 12/14/2025 (Source: rittal.com/us-en)



SZ 2388.650 - Rail for EMC shielding bracket and strain relief

Combined rails for strain relief and EMC contacting of inserted cables.





Features

SZ 2388.650
C rail to accommodate cable clamps T-head slots in 40 mm hole pattern for cable attachment using cable ties
Combined rails for strain relief and EMC contacting of inserted cables.
Additional contacting on the left or right of the rail via existing holes (9 mm diameter) Prepared for tool-free assembly of EMC shielding bracket
Extruded aluminum section
Chrome-free passivated
1 rail 2 retaining brackets Assembly components
553 mm 21.8 ″
On the horizontal/vertical enclosure section on a mounting plate, may also be fitted without a retaining bracket

© Rittal 2025

Features

Suitable for	Enclosure type: VX TS Width: = 600 mm Enclosure type: VX TS Width: = 23.6 "
Packaging unit	1 pc(s).
Net weight	0.5
Gross weight	0.58
Customs tariff number	76042990
EAN	4028177698918
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234

© Rittal 2025 3