


# Rittal – The System.

Faster – better – everywhere.



## SZ 2388.650

## Rail

State: 5/11/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2388.650 - Rail for EMC shielding bracket and strain relief

Combined rails for strain relief and EMC contacting of inserted cables.



## Features

|                      |   |
|----------------------|---|
| Model No.            | SZ 2388.650   |
| Version              | C rail to accommodate cable clamps<br>T-head slots in 40 mm hole pattern for cable attachment using cable ties  |
| Product description  | Combined rails for strain relief and EMC contacting of inserted cables.   |
| Benefits             | Additional contacting on the left or right of the rail via existing holes (9 mm diameter)<br>Prepared for tool-free assembly of EMC shielding bracket |
| Material             | Extruded aluminum section   |
| Surface finish       | Chrome-free passivated  |
| Supply includes      | 1 rail<br>2 retaining brackets<br>Assembly components   |
| Length               | 553 mm<br>21.8 "  |
| Installation options | On the horizontal/vertical enclosure section<br>on a mounting plate, may also be fitted without a retaining bracket                                   |

# Features

---

|                       |  |
|-----------------------|--|
| Suitable for          | Enclosure type: VX<br>TS<br>Width: = 600 mm<br>Enclosure type: VX<br>TS<br>Width: = 23.6 ~ |
| Packaging unit        | 1 pc(s).   |
| Net weight            | 0.5 kg   |
| Gross weight          | 0.58 kg  |
| Customs tariff number | 76042990   |
| ETIM 9                | EC002625   |
| ETIM 8                | EC002625   |
| ECLASS 8.0            | 27189234   |
| Product description   | SZ Rail, for EMC rail and stain relief, for W: 600 mm                                      |