

# Rittal – The System.

Faster – better – everywhere.



## SK 3138.000

## Roof-mounted fan, roof vent

State: 4/23/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3138.000 - Roof-mounted fan, roof vent

The new generation of roof-mounted fans is one system for all sizes: only one mounting cut-out is needed for all output categories. Air routing with minimal pressure losses ensures a high level of efficiency, while an innovative clamping attachment supports a high protection category of IP54.



## Features

Model No.	SK 3138.000
Version	roof-mounted
Product description	Roof-mounted fan with a high protection category and flexible installation from the inside or outside.
Color	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	without fan motor
Dimensions	Width: 400 mm Height: 133 mm Depth: 400 mm Width: 15.7 " Height: 5.24 " Depth: 15.7 "
Installation depth	27.5 mm 1.08 "

# Features

---

Mounting cut-out	Width of opening: 258 mm Depth of opening: 258 mm Width of opening: 10.2 " Depth of opening: 10.2 "
Protection category IP to IEC 60529	IP 21 without filter mat IP 54 including pleated filter
Protection category NEMA	NEMA 12
Note	A chopped fiber filter can be used to increase the protection category to IP 55 (see accessories). To improve energy efficiency and increase equipment service life, we recommend thermostats or temperature displays.
Operating temperature range	-20 °C...55 °C -4 °F...131 °F
Storage temperature range	-40 °C...70 °C -40 °F...158 °F
Packaging unit	1 pc(s).
Net weight	3.2 kg
Gross weight	3.5 kg
Customs tariff number	84145915
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
Product description	SK roof-mounted fan, roof vent, WHD: 400 x 133 x 400 mm, without fan motor

---

# Approvals

---

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
-----------	---

---

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK