


Rittal – The System.

Faster – better – everywhere.



SK 3149.007

Roof-mounted fan, roof vent

State: 7/27/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3149.007 - Roof-mounted fan, roof vent

Can be installed on any sufficiently large roof surface, air throughput 211.89 cfm.

Features

Model No.	SK 3149.007
Version	Unit ready for connection with built-in radial fan
Product modification	Mounting cutouts are not compatible. Adapter frame 5050.700 is required when using the roof panel.
Material	Carbon steel, spray finished
Color	RAL 7035
Supply includes	Sealing and assembly components Drilling template Connection cable (3 m)
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 42 W
Rated current max.	At 50 Hz: 0.2 A
Dimensions	Width: 420 mm Height: 95 mm Depth: 340 mm Width: 16.5 " Height: 3.74 " Depth: 13.4 "
Mounting cut-out	Width of opening: 345 mm Depth of opening: 265 mm Width of opening: 13.6 " Depth of opening: 10.4 "
Protection category IP to IEC 60529	IP 43
Note	Via additional installation of the filter holder with filter mat, a protection category of IP 44 is achieved with roof vent 3148.007.

Features

Operating temperature range	-10 °C...60 °C 14 °F...140 °F
Noise pressure level	At 50 Hz: 53 dB(A)
Packaging unit	1 pc(s).
Net weight	5.824
Gross weight	6.131
Customs tariff number	84145915
EAN	4028177165342
ECLASS 8.0	27180716

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------