

# Rittal – The System.

Faster – better – everywhere.



## SK 3164.620 Roof-Mounted Fans

State: 6/16/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3164.620 - Roof-Mounted Fans for VX, VX IT

Roof-mounted fan for the office sector with minimal noise level (40 dB) and high volumetric flow (unimpeded air flow 1500 m<sup>3</sup>/h).



## Features

Model No.	SK 3164.620
Benefits	Easy assembly, the roof plate variant eliminates the need to create mounting cut-outs Wired ready for connection
Material	Carbon steel, spray finished
Color	RAL 7035
Supply includes	Roof-Mounted Fans Assembly components
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 0.3 A At 60 Hz: 0.35 A
Dimensions	Width: 800 mm Height: 240 mm Depth: 800 mm Width: 31.5 " Height: 9.45 " Depth: 31.5 "
Protection category IP to IEC 60529	Internal circuit, IP 54
Note	Reduction of the specified air flow to 800 m <sup>3</sup> /h at 40 Pa counter-pressure using two ventilated base/plinth trim panels

# Features

Operating temperature range	20 °C...55 °C 68 °F...131 °F
Packaging unit	1 pc(s).
Net weight	28.5
Gross weight	30
Customs tariff number	84145915
EAN	4028177243248
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

# Approvals

Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK