Rittal – The System.

Faster - better - everywhere.





HD 2410.131 Cable gland HD

State: 11/18/2025 (Source: rittal.com/us-en)




HD 2410.131 - Cable gland HD

The design is more compact and the locknut is already included.







Features

Model No.	HD 2410.131
Version	EMC
Benefits	Smooth, solid exterior surfaces effectively prevent the accumulation of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Production and packaging of food and beverages Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Incl. lock nut
Dimensions	Thread: M25 x 1.5
For cable diameters	12 - 17 mm 0.47 - 0.67 ″

© Rittal 2025

Features

Operating temperature range	-20 °C100 °C -4 °F212 °F
Protection category IP to IEC 60 529	IP69 / IPX8 (5 bar, 30 min)
Type rating according to UL 50E	Type 1
	Type 2
	Type 4
	Type 4X
	Type 12
	Type 12K
	Type 13
Packaging unit	5 pc(s).
Net weight	0.54
Gross weight	0.59
Customs tariff number	73072980
EAN	4028177928664
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

Approvals

Approvals	UL + C-UL (listed)
	VDE

© Rittal 2025 3