

**Rittal – The System.**

Faster – better – everywhere.



**SZ 2411.631**

**Cable gland, polyamide**

State: 7/8/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2411.631 - Cable gland, polyamide

Integrated clamping membranes ensure safe tightening and cable-friendly strain relief.

## Features

Model No.	SZ 2411.631
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief that protects the cables
Material	Polyamide 6 Seal: CR/NBR
Color	RAL 7035
Protection category IP to IEC 60529	IP 68 (5 bar, 30 min.)
Dimensions	Height: 35.5 mm Height: 1.4 "
Thread	M25 x 1.5
Thread length	8 mm 0.31 "
Min. cable diameter	10 mm 0.39 "
Max. cable diameter	17 mm 0.67 "
Operating temperature range	-30 °C...100 °C -22 °F...212 °F
torque	5 Nm
Width across flats	29 mm
Dimensions	Thread: M25 x 1.5 Thread length: 8 mm Thread: M25 x 1.5 Thread length: 0.31 "

# Features

---

Type rating according to UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Packaging unit	25 pc(s).
Net weight	0.475 kg
Gross weight	0.495 kg
Customs tariff number	39269097
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	SZ Cable gland, polyamide, size: M25x1,5, for cables ø 10-17 mm

---

# Approvals

---

Approvals	CSA + CSAus UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK

---