Rittal – The System.

Faster – better – everywhere.





SZ 2411.861 Cable gland, brass

State: 11/17/2025 (Source: rittal.com/us-en)



SZ 2411.861 - Cable gland, brass

Integrated clamping membranes ensure safe tightening and cable-friendly strain relief.

Features

Model No.	SZ 2411.861
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief that protects the cables
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
Protection category IP to IEC 60 529	IP 68 (5 bar, 30 min.)
Dimensions	Height: 52 mm Height: 2.05 ″
Thread	M50 x 1.5
Thread length	9 mm 0.35 ″
Min. cable diameter	27 mm 1.06 ″
Max. cable diameter	38 mm 1.5 ″
Operating temperature range	-40 °C100 °C -40 °F212 °F
torque	35 Nm
Width across flats	58 mm
Dimensions	Thread: M50 x 1.5 Thread length: 9 mm Thread: M50 x 1.5 Thread length: 0.35 "

© Rittal 2025

Features

Type rating according to UL 50E	Type 1
	Type 4
	Type 4X
	Type 12
	Type 13
Packaging unit	2 pc(s).
Net weight	0.6
Gross weight	0.678
Customs tariff number	74198090
EAN	4028177810037
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

Approvals

Approvals	UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3