

Rittal – The System.

Faster – better – everywhere.



SK 3178.801

Wall-mounted cooling unit Blue e+ S

State: 2/24/2026 (Source: rittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3178.801 - Wall-mounted cooling unit Blue e+ S

1023.64 - 3412.14 BTU/h

Blue e+ S cooling units with proven Blue e+ technology offer the world's highest energy efficiency. This is also linked with a reduction in the CO₂ footprint of machinery and equipment. In a new design and with many smart functions.

Features

Model No.	SK 3178.801
Version	wall-mounted
Benefits	<p>Helps make production climate-neutral thanks to average energy savings of 75% and reduction of CO₂ footprint</p> <p>Universal compatibility due to multi-voltage capability and country-specific approvals</p> <p>Intelligent and easy monitoring via IoT interface</p> <p>Convenient operation with the Rittal Scan & Service App</p>
Material	Carbon steel
General color	RAL 7035
Color	Housing: RAL 7035 Louvered grille: RAL 7012
Supply includes	Assembly components Wired ready for connection (plug-in terminal strip)
Options	<p>For remote monitoring and networking of cooling units and chillers, use the Blue e+ Generation IoT Interface, item number 3124.300.</p> <p>Increase machine availability and process safety by remote monitoring of device data, condition, and system messages.</p>
Total cooling output to DIN EN 14511	<p>Cooling output L35 L35/50 Hz: 0.3 kW</p> <p>Cooling output L35 L35/60 Hz: 0.3 kW</p> <p>Cooling output L35 L50/50 Hz: 0.22 kW</p> <p>Cooling output L35 L50/60 Hz: 0.22 kW</p> <p>Cooling output L35 L35/50 Hz: 1,024 BTU/h</p> <p>Cooling output L35 L35/60 Hz: 1,024 BTU/h</p> <p>Cooling output L35 L50/50 Hz: 751 BTU/h</p> <p>Cooling output L35 L50/60 Hz: 751 BTU/h</p>

Features

Rated operating voltage	110 V - 240 V, 1~, 50 Hz/60 Hz
Note	<p>Please observe the assembly instructions.</p> <p>When the software is downloaded, a contract is concluded between the contractual partner and Rittal for the free use of the software in accordance with these license conditions.</p> <p>Only for semi-outdoor use (see instructions for description)</p>
Note on Model No.:	Tolerance: 110 V -10% (99 V) and 240 V +10% (264 V)
Rated output	0.22 kW
Air throughput (unimpeded air flow)	External circuit: 366.6 m ³ /h Internal circuit: 366.6 m ³ /h External circuit: 215.8 cfm Internal circuit: 215.8 cfm
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.01 Refrigeration factor L35 L35 (EER) 60 Hz: 2.01
Version	wall-mounted
Dimensions	Width: 300 mm Height: 570 mm Depth: 159 mm Width: 11.8 " Height: 22.4 " Depth: 6.26 "
Required mounting cut-out	Width of opening: 280 mm Cut-out height: 550 mm Width of opening: 11 " Cut-out height: 21.7 "
Protection category IP to EN 60 529	Internal circuit IP 55
Protection category NEMA	UL Type 1 UL Type 12
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.13 kg Global Warming Potential (GWP): 631 CO ₂ equivalent (CO ₂ e): 0.08 t Refrigerant: R-513A Quantity: 0.3 lb.

Features

Temperature control	e+ controller (factory setting +35 °C)
Operating temperature range	-20 °C...60 °C -4 °F...140 °F
Storage temperature range	-40 °C...70 °C -40 °F...158 °F
Operating temperature range of refrigerant circuit (active)	3 °C...60 °C
Operating temperature range of heat pipe	-20 °C...45 °C
Setting range	20 °C...50 °C 68 °F...122 °F
Rated power Pel	Rated power L35 L35/50 Hz: 0.15 kW Rated power L35 L35/60 Hz: 0.15 kW Rated power L35 L50/50 Hz: 0.18 kW Rated power L35 L50/60 Hz: 0.18 kW
Permissible operating pressure (p. max.)	32 bar 464.1 PSI
Packaging unit	1 pc(s).
Net weight	12.2 kg
Gross weight	13.2 kg
Customs tariff number	84158200
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK Cooling unit Blue e+ S, wall-mounted, 1024 BTU/h 110-240 V, 1~, 50-60 Hz, carbon steel, WHD: 300 x 570 x 159 mm

Approvals

Approvals

Approvals	UL + C-UL (listed) UL + C-UL - FTTA
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation