

# Rittal – The System.

Faster – better – everywhere.



## SZ 2500.220 LED system light

State: 12/9/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2500.220 - LED system light

LED system light - the first light designed especially for enclosures! Advanced LED technology provides even more light into the last recess.



## Features

Model No.	SZ 2500.220
Version	without socket
Benefits	Optimum illumination of the entire enclosure Option of clip-on, screw or magnetic attachment A configuration to suit every application
Version	90° rotating connector Adjustable light distribution
Material	Light body: Extruded aluminum Light cover: polycarbonate Light ends: PC-ABS
Color	Enclosure: RAL 7016
Supply includes	Assembly screws
Rated power	11 W
Connection options	Power Supply, 2-pole Through-wiring, 2-pole Door-operated switch
Protection category	III (SELV)

# Features

Light – installation type	Screw fastening Clip fastening Magnetic fastener (accessories)
Installation options	Directly onto the enclosure section with 25 mm pitch pattern
Luminous flux	900 lm
Light color	4000 K (neutral white)
Note	Connection accessories should be ordered separately
Dimensions	Width: 437 mm Height: 75 mm Depth: 23 mm Width: 17.2 " Height: 2.95 " Depth: 0.91 "
Operating temperature range	-20 °C...55 °C -4 °F...131 °F
Rated operating voltage	24 V (DC)
Protection category IP to IEC 60529	IP 20
Packaging unit	1 pc(s).
Net weight	0.394
Gross weight	0.54
Customs tariff number	94054990
EAN	4028177806979
ETIM 9	EC000321
ETIM 8	EC000321
ECLASS 8.0	27189241

## Approvals

# Approvals

---

Approvals

CQC  
CQC-CCC  
ENEC  
UL + C-UL (listed)

---

Explanations

Declaration of conformity  
Declaration of conformity UK