Rittal – The System.

Faster – better – everywhere.



SZ 2500.220
LED system light

State: 11/9/2026 (Source: www.rittal.com/us-en)

SZ 2500.220 - LED system light

LED system light - the first light designed especially for enclosures! Advanced LED technology provides even more light into the last recess.





Features

Model No.	SZ 2500.220
Version	without socket
Benefits	Optimum illumination of the entire enclosure Option of clip-on, screw or magnetic attachment A configuration to suit every application
Version	90° rotating connector Adjustable light distribution
Material	Light body: Extruded aluminum Light cover: polycarbonate Light ends: PC-ABS
Color	Enclosure: RAL 7016
Supply includes	Assembly screws
Rated power	11 W
Connection options	Power Supply, 2-pole Through-wiring, 2-pole Door-operated switch
Protection category	III (SELV)

© Rittal 2026

Features

Light – installation type	Screw fastening Clip fastening Magnetic fastener (accessories)
Installation options	Directly onto the enclosure section with 25 mm pitch pattern
Luminous flux	900 lm
Light color	4000 K (neutral white)
Note	Connection accessories should be ordered separately
Dimensions	Width: 437 mm Height: 75 mm Depth: 23 mm Width: 17.2 ″ Height: 2.95 ″ Depth: 0.91 ″
Operating temperature range	-20 °C...55 °C -4 °F...131 °F
Rated operating voltage	24 V (DC)
Protection category IP to IEC 60 529	IP 20
Packaging unit	1 pc(s).
Net weight	0.394 kg
Gross weight	0.54 kg
Customs tariff number	94054940
ETIM 9	EC000321
ETIM 8	EC000321
ECLASS 8.0	27189241
Product description	SZ System Light LED, 900 Lumen, L: 437 mm, 24 V DC

Approvals

Approvals

Approvals	CQC ENEC UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK