
Rittal – The System.

Faster – better – everywhere.



AX 2508.020

Wall mounting bracket

State: 11/18/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AX 2508.020 - Wall mounting bracket for AX carbon steel, KX carbon steel, AX IT EL

Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces.

Features

Model No.	AX 2508.020
Product description	Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces.
Benefits	Screw-fastened directly from the rear with a self-tapping screw into the enclosure eyelet Simple location of the wall bracket on a pre-configured screw in the wall The wall mounting can be optimally adapted to the local conditions via various mounting positions As an alternative to a self-tapping screw, the holder can also be secured from the inside using a screw and nut Additional option for fastening with a nut for dynamic applications
Material	Carbon steel, zinc-plated
Supply includes	Wall mounting bracket Cover Caps Assembly components
Wall distance	20 mm 0.79 ″
Suitable for	Enclosure type: AX carbon steel KX carbon steel AX IT EL AX wall-mounted housing, 3-part
Type rating according to 508A	Type 1 Type 3R Type 4 Type 12
Packaging unit	4 pc(s).

Features

Net weight	0.44 kg
Gross weight	0.44 kg
PCF/VE (cradle-to-gate)	1.7 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	83025000
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234
Product description	SZ Wall mounting bracket, for AX and KX, sheet steel, wall distance: 20 mm

Approvals

Approvals	DNV UL + C-UL - FTTA