

Rittal – The System.

Faster – better – everywhere.



AX 2508.020

Wall mounting bracket

State: 4/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2508.020 - Wall mounting bracket for AX carbon steel, KX carbon steel, AX IT EL

Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces.

Features

| | |
|---------------------------------|---|
| Model No. | AX 2508.020 |
| Product description | Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces. |
| Benefits | Screw-fastened directly from the rear with a self-tapping screw into the enclosure eyelet Simple location of the wall bracket on a pre-configured screw in the wall The wall mounting can be optimally adapted to the local conditions via various mounting positions As an alternative to a self-tapping screw, the holder can also be secured from the inside using a screw and nut Additional option for fastening with a nut for dynamic applications |
| Material | Carbon steel, zinc-plated |
| Supply includes | Wall mounting bracket Cover Caps Assembly components |
| Wall distance | 20 mm 0.79 " |
| Suitable for | Enclosure type: AX carbon steel KX carbon steel AX IT EL AX wall-mounted housing, 3-part |
| Type rating according to UL 50E | Type 1 Type 3R Type 4 Type 12 |
| Packaging unit | 4 pc(s). |

Features

| | |
|-------------------------------------|--|
| Net weight | 0.44 kg |
| Gross weight | 0.44 kg |
| PCF/VE (cradle-to-gate) | 1.7 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 83025000 |
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | SZ Wall mounting bracket, for AX and KX, sheet steel, wall distance: 20 mm |

Approvals

| | |
|-----------|----------------------------|
| Approvals | DNV-GL UL + C-UL - FTTA |
|-----------|----------------------------|